

Anion Installation Guide

Accessories



A. Multifunction handshower



B. 150 cm stainless steel hose



C. Air-In Valve



D. O-Clean

* Consumables: Air-In Valve, Silicone Tube and Dustproof.

Anion handshower kit

A. Multifunction handshower

Material: ABS

Function: Multifunction

(Wide coverage/targeted massage spray)

Dimension: 90x28x128 mm

B. 150 cm stainless steel hose

Material: Stainless steel

Dimension: 150 cm

C. Air-In Valve

Dimension : 65x28.5 (OD) mm

Material: Stainless Steel

D. O-Clean OH0008

Power supply voltage: 100V-120V, 50/60Hz


Power consumption: 6W(max)

Size: 115(L)x50(W)x180(H)mm

Ozone output: 300mg/hr

Ozone Machine

Hand Shower



Installation Guide

1. Install the Air-In Valve onto the water outlet.
 2. Connect the hose to the Air-In Valve.
 3. Connect the hose to the handshower.
 4. Attach the Check Valve (the side with short silicone tube) to Ozone Machine's silicone tube port.
 5. Connect Air-In Valve and Check Valve with silicone tube.
- Plug in and press the power button at right side of the machine. Then the installation is completed.

* Water pressure difference will influence the outcome.

* This item is suitable for water pressure over 1.5 kg/cm²